

BINS

Pedal-operated bins



PP1303/PP1305/PP1312/
PP1321 White finish



PP1303C/PP1305C/PP1312C/
PP1321C Bright finish



PP1303CS/PP1305CS/PP1312CS/
PP1321CS Satin finish



PP1303B/PP1305B/
PP1312B
Black finish

General description

- Indoor circular body waste bins, 3L (PP1303...), 5L (PP1305...), 12L (PP1312...) or 20L (PP1321...) capacity, operated by means of a pedal, to rest directly on the floor.
- Suitable for washrooms and in-doors public areas. Models suitable for public use.
- Strong plastic inner bucket - easy to clean and to remove the bin liner.
- Smooth and silent closing lid that avoids bad odors.
- Sturdy carrying handle - easy to move the bin.


Components and materials

- PP1321/ PP1312/ PP1305/ PP1303:** steel white Epoxy finish.
- PP1321C/ PP1312C/ PP1305C/ PP1303C:** AISI 410 stainless steel, bright finish.
- PP1321CS/ PP1312CS/ PP1305CS/ PP1303CS:** 410 stainless steel, satin finish.
- PP1303B/ PP1305B/ PP1312B:** steel black Epoxy finish.
- BODY:** circular. Robust against shocks and misuse.
- LID:** circular. Silent and anti-odors. Lid opening based on hinge system made of thermoplastic material.
- BASE:** made of black thermoplastic, non-slip, insulates the cube bottom of moisture and makes the cube remain stable in place.
- INNER BUCKET:** made of polypropylene with metal handle, for easy removal and capacity of 3 L (PP1303 ...), 5 L (PP1305 ...), 12 L (PP1312) or 20 L (PP1321).
- PEDAL:** metallic with a piece of non-slip black thermoplastic attached on its top. Activates the opening of the lid by pressing.
- HANDLE:** metallic and located in the upper rear part of the bin to facilitate the transport.

Technical specifications

| Capacity | 3 L (PP1303...) 5 L (PP1305...) 12 L (PP1312...) 20 L (PP1321...) | | |
|--------------|--|------|------|
| Weight (net) | --- | C | CS |
| | (Kg) | (Kg) | (Kg) |
| PP1303... | 0,63 | 0,56 | 0,56 |
| PP1305... | 0,84 | 0,75 | 0,75 |
| PP1312... | 1,62 | 1,45 | 1,45 |
| PP1321... | 2,00 | 1,80 | 1,80 |

Dimensions



| | LØ (mm) | L1 (mm) | L2 (mm) | L3 (mm) |
|-----------|---------|---------|---------|---------|
| PP1303... | 168 | 226 | 250 | 226 |
| PP1305... | 205 | 264 | 275 | 264 |
| PP1312... | 249 | 320 | 392 | 320 |
| PP1321... | 290 | 362 | 450 | 362 |

Dimensions: ± 4%

Operation

Push with the foot the pedal to operate the lid opening.

Mediclinics, S.A., reserves the right to make changes and/or modifications to the products and their specifications without prior notice
© mediclinics S.A.

8-OP-DO-FT